

## Climatic and Temperature Chamber's Option

Designation	Description	Notes	Art. No.
Datalogger	<i>temperature USB and software</i>	-	MINI T
Datalogger	<i>temperature/humidity USB and software</i>	-	MINI T-RH
Digital recorder/controller	<i>digital recorder/controller</i>	-	ND-R
Digital recorder/controller	<i>module Ethernet and software</i>	-	ND-ES
USB storage data	<i>USB port for storage data</i>	-	UDB100
Programmer	<i>programmer 1 program 20 steps</i>	-	PG01020
Programmer	<i>addition 10 program 50 steps</i>	-	PG10050
Programmer	<i>addition 25 program 50 steps</i>	-	PG25100
Programmer	<i>addition 50 program 100 steps</i>	-	PG50200
RS485 Serial interface	<i>RS485 Serial interface for remote connection</i>	-	RS485
Interface converter RS485/USB	<i>RS485/USB interface converter</i>	-	RS485/USB
RS232 Serial interface	<i>RS232 Serial interface for remote connection</i>	-	RS232
Ethernet interface	<i>Ethernet interface for remote connection</i>	-	ETH100
Pt 100 temperature sensor	<i>additional Pt 100, with flexible cable installed with external connection</i>	-	SND20T
Humidity sensor	<i>additional humidity sensor unit</i>	-	SND80H
Water filtration system	<i>AS-Water 5 liters filtration system with automatic regeneration for the removal of salts of calcium and magnesium</i>	-	ASW05
Water filtration system	<i>AS-Water 10 liters filtration system with automatic regeneration for the removal of salts of calcium and magnesium</i>	-	ASW10
Water filtration system	<i>intake system with on/off interior compartment and a mechanical timer for daily execution cycles</i>	-	SA100
Hair ventilation filter	<i>Hepa 14 filter</i>	-	HPA14
Hair ventilation filter	<i>G4 filter</i>	-	GF400
Boosted dehumidification system	<i>it allows to decrease the relative humidity up to 2% @ 20°C</i>	-	BDS020
CO2 system	<i>CO2 Regulation System for EN 12390-10</i>	-	CO200
Day/Night temperature simulation	<i>Day/Night temperature regulation</i>	-	GN100
Day/Night humidity simulation	<i>Day/Night humidity regulation</i>	-	GH100
Interior socket	<i>coverable universal 220-230 V</i>	-	PE100
Interior lighting	<i>neon illumination on shelf 10000 lux with photoperiod</i>	-	IR200
Interior lighting	<i>neon illumination on shelf 10000 lux with photoperiod 2 doors</i>	-	IR202
Interior lighting	<i>neon illumination on shelf 10000 lux with photoperiod 3 doors</i>	-	IR203
Interior lighting	<i>neon illumination on shelf 10000 lux dimmable adjusting light</i>	-	IRD200
Interior lighting	<i>LED illumination on shelf 10000 lux</i>	-	IRS200LED
Interior lighting	<i>opening door light</i>	-	IL100
Interior lighting	<i>neon illumination on lateral inner walls 10000 lux with photoperiod</i>	01	IL200
Interior lighting	<i>neon illumination on lateral inner walls 10000 lux with photoperiod 2 doors</i>	01	IL202
Interior lighting	<i>neon illumination on lateral inner walls 10000 lux with photoperiod 3 doors</i>	01	IL203
Interior lighting	<i>neon illumination on lateral inner walls 10000 lux dimmable adjusting light</i>	01	ILD200
Interior lighting	<i>neon illumination on lateral inner walls 10000 lux dimmable adjusting light 3 doors</i>	01	ILD203
Interior lighting	<i>LED illumination on lateral inner walls 10000 lux</i>	-	IRW200LED
Interior lighting	<i>dimmable adjusting light for individual lamp</i>	-	IS200
Interior lighting	<i>photoperiod 24h control</i>	-	FP100
Interior lighting	<i>specific illumination at request</i>	-	LTC100

## Climatic and Temperature Chamber's Option

Designation	Description	Notes	Art. No.
Inner door	<i>glass door</i>	-	GD100
Inner door	<i>lexan door</i>	-	SP100
Main door	<i>glass door (single)</i>	-	PV101
Main door	<i>glass door (double)</i>	-	PV102
Main door	<i>glass door (triple)</i>	-	PV103
Phorthole window	<i>phorthole with anti-fogging glass (Ispection window)</i>	-	GW100
Sterile flux vapor humidifier	<i>sterilised flux vapor humidifier</i>	-	UMS100
Pool system	<i>pools system for EN1348-2007</i>	-	SPS07
Pool system	<i>supply water tank system 25 liters</i>	-	WT025
Packaging	<i>wooden crate 130-310-370 liters</i>	-	PAC10
Packaging	<i>wooden crate 450-530 liters</i>	-	PAC20
Packaging	<i>wooden crate 810-1020-1180 liters</i>	-	PAC30
Packaging	<i>wooden crate 1830 liters</i>	-	PAC40
Packaging	<i>wooden boxes 130-310-370 liters</i>	-	PAW10
Packaging	<i>wooden boxes 450-530 liters</i>	-	PAW20
Packaging	<i>wooden boxes 810-1020-1180 liters</i>	-	PAW30
Packaging	<i>wooden boxes 1830 liters</i>	-	PAW40
Packaging	<i>fumigation treatment for wooden crate or boxes</i>	-	FTW10
Castor	<i>castors kit</i>	-	RT100
Access port with plug	<i>right</i>	-	FD100
Access port with plug	<i>left</i>	-	FL100
Access port with plug	<i>top</i>	-	FS100
Shelf, grill	<i>plastic coated with rails</i>	-	GP100
Shelf, grill	<i>reinforced, plastic coated with rails</i>	-	GP100R
Shelf, grill	<i>stainless steel with rails</i>	-	GP100X
Calibration report, temperature	<i>measurement in center of chamber at specified temperature</i>	-	CCT001
Calibration report, temperature	<i>temperature measurement incl. report, 9 measuring points at specified temperature</i>	-	CCT009
Calibration report, humidity	<i>measurement in center of chamber at specified humidity</i>	-	CCH001
Calibration report, humidity	<i>humidity measurement incl. report, 9 points at specified humidity</i>	-	CCH009
Surge protection device	<i>surge protection device for regulating and circuit control</i>	-	DPS100
Power supply 110 V 50-60 Hz	<i>power supply 110 V 50-60 Hz</i>	-	TE110
ISO 10977-ISO 18909-ICH	<i>ISO 10977-ISO 18909-ICH compliant Illumination</i>	-	CMP-10977-18909

## Climatic and Temperature Chamber's Option

---

Notes	Description
01	<i>The installation of wall illumination reduces the useful width of the shelves: for 130,310,370,810 net volume size is reduced of 100 mm for 450, 530, 1020, 1180 net volume size is reduced of 60 mm</i>