## MARATHON PRODUCTS

Our Single-use Temperature Logger with Real-Time LCD Display for Instant Acceptance or Quarantine Decisions.

**c\temp-LCD** is the revolutionary, single-use, pre-programmed, electronic temperature data recorder specifically designed for measuring temperatures during the transportation of refrigerated vaccines, biological material, chemicals, pharmaceuticals, and for documenting the transportation of perishable commodities. The ctemp-LCD is NIST-Traceable and comes with a Certificate of Conformance.

#### Functions include:

#### \_\_\_\_\_

- Internal Thermistor: accurately records time and temperatures for user selectable readings in Celsius or Fahrenheit.
- LCD display: Shows Current temperature, Max Temperature, Minimum Temperature, Run Time, Alarm Status, and Recording.

**Small Form Factor:** c\temp-lcd has an extended battery life and can endure rough handling. The internal software records the following: time mechanism, start time, sampling intervals, end description for special instructions, alarm values, recording status, measurement data, software version, serial and tracking number, model type and after the fact report generation options.

**Visual Alarms:** All our data loggers can be programmed with alarm limits. Should the temperature reach levels outside these limits, the LDC will display "ALARM." To start the recorder, simply press the start button!

**USB Interface:** To download recorded information, simply plug the optional USB Cradle into the standard USB port of your PC.

# MARATHON "

Cloud

Computing

Temperature Logger

Management

TRACEABILITY,

HACCP COMPLIANCE

logger customers can share data

and RH files remotely, anywhere,

HACCP rules and regulations for

all of your perishable shipments.

Marathon's Temperature data


and access their temperature


at anytime via the Internet.

Our cloud-based software

provides compliance with

MaxiThermal Software Highlights: Easy-to-use software provides clear graphs. Report Summary & Statistics File Manager, Note Attachment, Zoom, Elapsed Time or Date/Time View, Recorded View, Celsius or Fahrenheit. Data can be exported to other Windows programs such as spreadsheets, word-processing or databases. Available for Windows 98, NT, 2000, ME, XP and Windows 7. An Enterprise Software version and 21CFR Part 11 Compliant Software are available





## c\temp-LCD Specifications

| Memory:  | EEPROM, 8k Storage (7,680 data points)   |  |
|--|--|--|
| Temperature Range:   | -35°C to +50°C (-31°F to +122°F)   |  |
| Temperature Accuracy:  | ±0.2°C at 0° to 10°C, ±1.0°C at extremes<br>(±0.36°F at 32° to 50° F, ±1.8°F at extremes)  |  |
| Measurement Intervals:   | Pre-programmed from 2 seconds to months.<br>For example:<br>4 days = 0 min. 45 sec.<br>7 days = 1 min. 18 sec.<br>16 days = 2 min. 58 sec.<br>30 days = 5 min. 33 sec.<br>60 days = 11 min. 6 sec.<br>90 days = 16 min. 39 sec.<br>365 days = 1 hr. 4 min. 39 sec. |  |
| Temperature Sensor:  | NIST-traceable Precision SMT Thermistor  |  |
| Indicators:  | LCD Display. Start/Stop and Alarm  |  |
| High and low alarm limits:   | ALARM set by temperature and time.   |  |
| Computer Interface:  | USB Cradle   |  |
| Internal Software Provides:  | Times, Start time, Interval, User description, Alarm values,<br>Recording status, Measurement data, Software version,<br>Serial number, Model type   |  |
| Power Source:  | Lithium Battery (1 year operating, 3 year shelf life)  |  |
| Size:  |  | idth Depth<br>4 cm (1.3 in.) 0.9 cm (0.35 in.) |
| Weight:  | 56.7 g (2.0 oz.)   |  |
| Quantity:  | Minimum 20 units. Your order is shipped on the same day if the order is placed before 2 p.m. PST.  |  |
| Options:   | MaxiThermal software<br>USB cradle   |  |
| Serialization:   | This recorder is programmed at the factory with a unique serial number for positive tracking.  |  |
| Waterproof Enclosure:  | The product package is hermetically sealed to an IP66 rating.  |  |
| Recyclable: c\temp-LCD recorders are designed for single use, and we encourage recycling.<br>Please call Marathan Products for complete disposal or recycling instructions |  |  |

g. Please call Marathon Products for complete disposal or recycling instructions.

optional usb

cradle

## Please call 1-510-562-6450

for more information or to place an order.

### www.marathonproducts.com

627 McCormick St., San Leandro, CA 94577 • jnakagawa@marathonproducts.com Specifications subject to change without prior notice.

rev.04022015